

One-stop PURCHASE







weight wheel and touch screen. When it work, the rotating cylinder rotates at constant speed, meanwhile the weight wheel moves in line along the cylinder axis at the constant speed. Applicate the sample on the parchment (film length is 30cm), then stick the parchment on the rotating cylinder. Move the weight wheel to the starting point (cylinder left) and set the needed time (from 5hours to 20 hours) which it go over the whole distance (the length of cylinder). If the ink don't dry completely, then the weight wheel would leave a mark on the parchment blank space, till the test is finish. Obtain the test results by counting the ink traces on the parchment and rotating cylinder working speed.



Main Technical Parameters:

- ★ Power: 220V ± 22V 50Hz
- ★ Speed of Pressure: 2mm/r
- ★ Time of whole course: 5~20 (hour)
- ★ Circle Number of Whole Course: 120r
- ★ Overall dimensions: 500mm×200mm×220mm (L×W×H)
- ★ Mass of Pressure: 100g
- ★ Weight: 17kg
- ★ Ordering Information:

BGD 660——Automatic Drying Tester for Ink

Tel: +86-20-82169666 E-mail: sale: carish@biuged.com Service: service@biuged.com WhatsApp: +86-13316053991 Website: www.biuged.com